

Product data sheet

Specifications



combo lighting, mechanically held,
3P, 30A, no fuse, NEMA 1,
480-120V 60Hz

8903SMG70V81A3F4TX11

Price*: 2,493.00 USD

! Discontinued

Main

Type	S
------	---

Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	3P
Control Units	Push-button ON-OFF)
Pilot Light	Without pilot light
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Disconnecter Device Type	Non-fusible disconnect switch
Electrical Connection	Lugs
Height	22.99 in (584 mm)
Depth	8.35 in (212 mm)
Width	13.74 in (349 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications