


# 8903SMH1V03CG101P1

lighting contactor, electrically held, 30 A, 2 pole,  
NEMA 3R, 240/220V 60/50Hz



Price\*\* : 1,715.00 USD



8903SMH1V03CG101P1 has not been replaced. Please contact your customer care center for more information.

## Main

Product	Electrically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	2P
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs

## Environment

Enclosure Type	NEMA 3R painted sheet steel surface and photoelectric receptacle with cell
Product certifications	CSA UL listed

## Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	50
Returnability	N

Offer Sustainability

---

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

---

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---