

# Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,  
30 A, 2 pole, NEMA 3R, 277V  
60Hz

8903SMH1V04

! Discontinued

## Main

Product	Electrically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	277 V AC 60 Hz
Current Rating	30 A
Number Of Poles	2P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	12.28 in (312 mm)
Depth	7.13 in (181 mm)
Width	8.82 in (224 mm)

## Environment

Enclosure Type	NEMA 3R Stainless Steel surface none
Product Certifications	UL Listed CSA

## Ordering and shipping details

Category	21325-8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	28.34 lb(US) (12.855 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------