

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 3 pole, open, 208V 60Hz

8903SMO2V08

Discontinued

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Current Rating	30 A
Number Of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	3.50 in (89 mm)
Depth	4.21 in (107 mm)
Width	3.23 in (82 mm)

Environment

Enclosure Type	Not rated (open device) surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21325-8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	2.71 lb(US) (1.229 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------