

Product data sheet

Specifications



NIGHT-MASTER, combo lighting contactor, 60 A, 3P, fuse, NEMA 3R, 480-120V 60Hz

8903SPC63V81C6C33FF4G101T

! Discontinued

Main

Type	Night-Master
------	--------------

Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	60 A
Number Of Poles	3P
Control Units	Key-operated selector switch ON-OFF)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Disconnecter Device Type	Fusible disconnect switch R, 60 A 600 V
Electrical Connection	Lugs
Height	38.86 in (987 mm)
Depth	10.43 in (265 mm)
Width	15.00 in (381 mm)

Environment

Enclosure Type	NEMA 3R painted sheet steel surface photoelectric receptacle with cell
Product Certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Category	21326-8903 S*C
Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.