

# Product data sheet


## Characteristics

# 8903SQA71V81A3FF4T

combo lighting, mechanically held, 3P, 100A,  
600V fuse, NEMA 12, 480-120V 60Hz



Price\*\* : 5,084.00 USD



8903SQA71V81A3FF4T has not been replaced. Please contact your customer care center for more information.

### Main

Type	S
------	---

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Line Rated Current	100 A
Number of Poles	3P
Control Units	Push-button (ON-OFF)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Electrical connection	Lugs
Height	42.01 in (1067 mm)
Depth	10.59 in (269 mm)
Width	15.24 in (387 mm)

### Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface and none
Product certifications	UL listed file E16151 CCN NRNT

### Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	19.199999999999999
Returnability	N

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---