

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
200 A, 3 pole, NEMA 1, 480-120V
60Hz

8903SVG2V81CFF4P1T

Price*: 5,972.00 USD

! Discontinued

Main

| | |
|---------|--------------------------------------|
| Product | Electrically Held Lighting Contactor |
| Type | S |

Complementary

| | |
|-------------------------|--|
| Control Circuit Voltage | 480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit |
| Current Rating | 200 A |
| Number Of Poles | 3P |
| Control Units | Selector switch 3 positions HAND-OFF-AUTO) |
| Pilot Light | Red indicator on incandescent |
| Auxiliary Contacts | Without |
| Control Circuit Fusing | 2 fuses primary circuit 1 fuse secondary circuit |
| Other Options | None |
| Electrical Connection | Lugs |
| Height | 39.13 in (994 mm) |
| Depth | 10.24 in (260 mm) |
| Width | 22.17 in (563 mm) |

Environment

| | |
|------------------------|---|
| Enclosure Type | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 16.48 lb(US) (7.476 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|