

# Product data sheet

Specifications

SQUARE D



combo lighting, electrically held,  
3P, 200A, 600V fuse, NEMA 1,  
480-120V 60Hz

8903SVG61V81AF4P2T

Price\*: 8,564.00 USD

! Discontinued

## Main

Type	S
------	---

## Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	200 A
Number Of Poles	3P
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Electrical Connection	Lugs
Height	50.00 in (1270 mm)
Depth	10.67 in (271 mm)
Width	15.98 in (406 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL listed file E16151 CCN NRNT

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	113.00 lb(US) (51.256 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications