

Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 300 A, 3 pole, NEMA 1, 480/440V 60/50Hz

8903SXG14V06R64X01

Price*: 11,115.00 USD

! Discontinued

Main

Type	S
------	---

Complementary

Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Current Rating	300 A
Number Of Poles	3P
Auxiliary Contacts	1 NC
Electrical Connection	Lugs
Height	44.21 in (1123 mm)
Depth	12.83 in (326 mm)
Width	17.20 in (437 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	135.00 lb(US) (61.235 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications