

Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 400 A, 3 pole, NEMA 1, 480/440V 60/50Hz

8903SYG17V06R64X01

Price*: 26,199.00 USD

! Discontinued

Main

| | |
|------|---|
| Type | S |
|------|---|

Complementary

| | |
|-------------------------|----------------------------------|
| Control Circuit Voltage | 480 V AC 60 Hz 440 V AC 50 Hz |
| Current Rating | 400 A |
| Number Of Poles | 3P |
| Auxiliary Contacts | 1 NC |
| Electrical Connection | Lugs |
| Height | 65.75 in (1670 mm) |
| Depth | 13.11 in (333 mm) |
| Width | 20.20 in (513 mm) |

Environment

| | |
|------------------------|---|
| Enclosure Type | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 210.00 lb(US) (95.254 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications