

# Product data sheet

Specifications

SQUARE D



## CONTACTOR 600VAC 40AMP DPA +OPTIONS

8910DPA43V14Y239Y181

! Discontinued

### Main

Device Short Name	DPA
-------------------	-----

### Complementary

Line Rated Current	40 A
Depth	3.12 in (79.25 mm)
Height	4 in (101.60 mm)
Locked Rotor Rated Current	240 A 230 V AC 200 A 460 V AC 160 A 575 V AC
Maximum Horse Power Rating	3 hp 115 V AC, 1 phase 7.5 hp 230 V AC, 1 phase 10 hp 230 V AC, 3 phase 20 hp 460/575 V AC, 3 phase
Mounting Support	panel
Number Of Poles	3
Width	2.5 in (63.50 mm)

### Environment

Product Certifications	UL listed file E42240 CCN NLDX CSA LR25490 class 3211 04
------------------------	---

### Ordering and shipping details

Category	21344-8910 DPA 4_(40 AMP)
Discount Schedule	CP1B
Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
<b>California Proposition 65</b>	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>