

# Product data sheet

Specifications



Pump Panel, NEMA Type S, Well Guard, Size 5, 270A, 10 kA SSCR, 200 HP, 400A Class H and K fuse clip, Motor Logic SSOLR, 480 VAC 60 Hz coil, NEMA 3R

8940SSG4200

Product availability: Stock - Normally stocked in distribution facility

Price\*: 16,286.00 USD

## Main

Product	Well-Guard Control
Type	class 8940 type SS
Device Application	Pumping

## Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	270 A
Number Of Poles	3
Horsepower Rating	200 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated Fuse Rating	400 A
Fuse Type	H or K
Thermal Overload Type	Motor Logic solid state class 10/20
Protection Type	Overload Phase loss Phase unbalance
Device Mounting	Surface
Electrical Connection	Screw terminal
Nema Size	5
Height	74.49 in (1892 mm)
Width	23.50 in (597 mm)
Depth	17.56 in (446 mm)

## Environment

Nema Rating	NEMA 3R
-------------	---------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Type	Weatherproof enclosure indoor/outdoor
Product Certifications	UL Listed NEMA

## Ordering and shipping details

Category	US10CP121392
Discount Schedule	0CP1
Gtin	785901325574
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	74.02 in (188.0 cm)
Package 1 Width	14.02 in (35.6 cm)
Package 1 Length	22.99 in (58.4 cm)
Package 1 Weight	390.00 lb(US) (176.901 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability


**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Pvc Free

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>