

# Product data sheet

Specifications



Pump Panel, NEMA Type S, Well Guard, oil field, Size 1, 27A, 10HP, 30A fusible disconnect, melting alloy overload, 440/480VAC 50/60Hz coil, NEMA 3R

8940WC3S2V06Y61

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 2,109.00 USD

## Main

Product	Well-Guard Control
Type	S2
Device Application	Pumping

## Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Line Rated Current	27 A
Number Of Poles	3
Horsepower Rating	10 hp 480 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Disconnect Type	Fusible disconnect switch
Associated Fuse Rating	30 A
Fuse Type	H or K
Thermal Overload Type	Motor Logic solid state class 10/20
Protection Type	Overload
Device Mounting	Surface
Electrical Connection	Screw terminal
Nema Size	1
Height	38.50 in (978 mm)
Width	20.43 in (519 mm)
Depth	9.41 in (239 mm)

## Environment

Nema Rating	NEMA 3R
Enclosure Type	Rainproof enclosure indoor/outdoor

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	UL Listed NEMA
------------------------	-------------------

## Ordering and shipping details

Category	US10CP121393
Discount Schedule	0CP1
Gtin	785901025818
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.99 in (33.0 cm)
Package 1 Width	41.10 in (104.4 cm)
Package 1 Length	21.69 in (55.1 cm)
Package 1 Weight	92.00 lb(US) (41.731 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	6
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	42.00 in (106.68 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	585.53 lb(US) (265.59 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>