





Complete control station, Harmony 9001B, selector switch, hand-off-auto, 5A, 600V AC, NEMA 1

9001BG112

Product availability: Stock - Normally stocked in distribution facility

Price\*: 86.00 USD

### Main

| Range Of Product          | Harmony 9001B            |
|---------------------------|--------------------------|
| Product Or Component Type | Complete control station |
| Device Short Name         | 9001BG                   |

# Complementary

| Control Station Composition    | 1 push-button HAND-OFF-AUTO |  |
|--------------------------------|-----------------------------|--|
| Contacts Type And Composition  | 1 NO + 1 NC                 |  |
| Connections - Terminals        | Screw clamp terminal        |  |
| [le] Rated Operational Current | 5 A 600 V                   |  |
| Device Mounting                | Surface                     |  |
| Type Of Installation           | llation Indoor              |  |

#### **Environment**

| Nema Degree Of Protection    | NEMA 1  |
|------------------------------|---|
| Product Certifications       | CE<br>CSA LR25490 class 3211 03<br>UL listed file E42259 CCN NKCR |
| Environmental Characteristic | Standard environment  |

## Ordering and shipping details

| Category          | US10CS121421 |  |
|-------------------|--------------|--|
| Discount Schedule | 0CS1         |  |
| Gtin              | 785901390138 |  |
| Returnability     | Yes          |  |
| Country Of Origin | US           |  |

## **Packing Units**

| Unit Type Of Package 1       | PCE               |
|------------------------------|-------------------|
| Number Of Units In Package 1 | 1                 |
| Package 1 Height             | 2.20 in (5.6 cm)  |
| Package 1 Width              | 2.52 in (6.4 cm)  |
| Package 1 Length             | 4.02 in (10.2 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight

8.96 oz (254.0 g)

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

# Well-being performance

| <b>⊘</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>9</b> | Toxic Heavy Metal Free     |     |
| <b>9</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

# **Certifications & Standards**

| Reach Regulation          | REACh Declaration  |
|---------------------------|--|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration  |
| China Rohs Regulation     | China RoHS declaration   |
| Circularity Profile       | End of Life Information  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

### **Dimensions Drawings**

## **Approximate Dimensions**

