# Product data sheet

Specification





Head for illuminated push button, Harmony 9001K, metal, projecting, without cap, 30mm, spring return, 110...120V

9001K2L1

Product availability: Stock - Normally stocked in distribution facility

Price\*: 143.00 USD

#### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for illuminated push-button
Device Short Name	К
Operator Additional Information	Without quard

## Complementary

Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Light Source	Incandescent bulb	
Bulb Base	BA 9s	
Light Block Supply	Via transformer	
Contacts Type And Composition	Without contact block	
[le] Rated Operational Current	10 A, AC-15 10 A, DC-13	
Device Presentation	Basic element	
Cap/Operator Or Lens Colour	Without cap	
[Us] Rated Supply Voltage	110120 V	
Light Block Supply	Via integral transformer	
Operator Profile	Projecting	
Type Of Operator	Spring return	
Supply Frequency	5060 Hz	
Size	30 mm	

#### **Environment**

Product Certifications	NEMA	
	UL listed file E42259 CCN NKCR	
	CE	
	CSA LR 25490 class 3211 03	
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13	

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901178545
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	8.16 oz (231.332 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov