# Product data sheet

Specifications



# PUSH BUTTON 600VAC 10A 30MM T-K

9001K2L1CH13

- () Discontinued on: Dec 2, 2020
- (!) End-of-service on: Dec 31, 2020



### Main

| Range Of Product                | Harmony 9001K           |
|---------------------------------|-------------------------|
| Product Or Component Type       | Illuminated push-button |
| Device Short Name               | к                       |
| Type Of Operator                | spring return           |
| Operator Profile                | Clear projecting        |
| Operator Additional Information | Without guard           |

## Complementary

| · · · · · · · · · · · · · · · · · · · |                            |
|---------------------------------------|----------------------------|
| Bezel Material                        | Chromium plated metal      |
| Mounting Diameter                     | 1.18 in (30 mm)            |
| Light Source                          | incandescent               |
| Bulb Base                             | BA 9s                      |
| Light Block Supply                    | Via integral transformer   |
| [Us] Rated Supply Voltage             | 110120 V AC                |
| Contacts Type And Composition         | 1 C/O                      |
| Connections - Terminals               | Screw clamp terminals      |
| Operating Position                    | Any position               |
| [le] Rated Operational Current        | 10 A, AC-15<br>10 A, DC-13 |
| Contact Operation                     | Standard                   |
| Device Presentation                   | Complete product           |
|                                       |                            |

### Environment

| Product Certifications    | CSA LR 25490 class 3211 03<br>NEMA<br>UL listed file E42259 CCN NKCR<br>CE |
|---------------------------|--|
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13  |

# Ordering and shipping details

| Category          | 21426-9001 K (NOT KA,KM,KX) |  |
|-------------------|-----------------------------|--|
| Discount Schedule | CS1                         |  |
| Returnability     | No                          |  |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin

MX

#### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

## **Certifications & Standards**

| Reach Regulation          | REACh Declaration  |
|---------------------------|--|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)   |
| China Rohs Regulation     | China RoHS declaration   |
| Environmental Disclosure  | Product Environmental Profile  |
| Weee                      | The product must be disposed on European Union markets following specific waste<br>collection and never end up in rubbish bins.  |
| Circularity Profile       | No need of specific recycling operations   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead<br>compounds, which is known to the State of California to cause cancer and birth<br>defects or other reproductive harm. For more information go to<br>www.P65Warnings.ca.gov |