





Complete illuminated push button, Harmony 9001K, metal, projecting, red, 30mm, spring return, LED red, 24...28V

9001K2L35LRR

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 153.00 USD

### Main

| Range Of Product          | Harmony 9001K                    |
|---------------------------|----------------------------------|
| Product Or Component Type | Head for illuminated push-button |
| Device Short Name         | 9001K                            |
| Mounting Diameter         | 1.18 in (30 mm)                  |
| Light Source              | Red LED                          |

## Complementary

| Bezel Material                | Metal                    |
|-------------------------------|--------------------------|
| Shape Of Signaling Unit Head  | Round                    |
| Type Of Operator              | spring return            |
| Operator Profile              | Red projecting, unmarked |
| Bulb Base                     | BA 9s                    |
| Light Block Supply            | Direct 2428 V AC/DC      |
| Contacts Type And Composition | Without contact block    |
| Mechanical Durability         | 5000000 cycles           |
| Operating Position            | Any position             |
| Net Weight                    | 0.37 lb(US) (0.166 kg)   |
| Cap/Operator Or Lens Colour   | Red                      |
| [Us] Rated Supply Voltage     | 2428 V                   |
| Light Source Colour           | Red                      |
| Type Of Operator              | Spring return            |
| Operator Profile              | Projecting               |

### **Environment**

| Standards | UL 508           |  |
|-----------|------------------|--|
|           | CSA C22.2 No 14  |  |
|           | EN/IEC 60947-1   |  |
|           | JIS C 852        |  |
|           | EN/IEC 60947-5-4 |  |
|           | JIS C 4520       |  |
|           | EN/IEC 60947-5-1 |  |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Product Certifications                   | UL 508<br>NEMA  |
|--|---|
| Protective Treatment                     | TC  |
| Ambient Air Temperature For Storage      | -40158 °F (-4070 °C)  |
| Ambient Air Temperature For<br>Operation | -13158 °F (-2570 °C)  |
| Vibration Resistance                     | 7 gn 2500 Hz)IEC 60068-2-6  |
| Shock Resistance                         | 50 gn IEC 60068-2-27  |
| Electrical Shock Protection Class        | Class II IEC 61140  |
| Ip Degree Of Protection                  | IP66 IEC 60529  |
| Nema Degree Of Protection                | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4 |

# Ordering and shipping details

| Category          | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1         |
| Gtin              | 785901714293 |
| Returnability     | No           |
| Country Of Origin | MX           |

# **Packing Units**

| Unit Type Of Package 1       | PCE                  |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 5.08 in (12.903 cm)  |
| Package 1 Width              | 2.00 in (5.08 cm)    |
| Package 1 Length             | 12.90 in (32.774 cm) |
| Package 1 Weight             | 8.00 oz (226.796 g)  |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | China RoHS declaration  |
| Environmental Disclosure  | Product Environmental Profile   |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |