

# Product data sheet

Specifications

SQUARE D



## PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

9001K2L35LYA

Discontinued on: Jan 23, 2021

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Complete illuminated push-button
Device Short Name	9001K
Mounting Diameter	1.18 in (30 mm)
Light Source	Yellow LED

### Complementary

Bezel Material	Chromium plated metal
Shape Of Signaling Unit Head	Round
Type Of Operator	spring return
Operator Profile	Amber projecting, unmarked
Bulb Base	BA 9s
Light Block Supply	Direct 24...28 V AC/DC
Mechanical Durability	5000000 cycles
Operating Position	Any position
Net Weight	0.37 lb(US) (0.166 kg)

### Environment

Standards	EN/IEC 60947-5-4 JIS C 4520 UL 508 EN/IEC 60947-1 JIS C 852 CSA C22.2 No 14 EN/IEC 60947-5-1
Product Certifications	NEMA UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Vibration Resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	00785901520108
Returnability	No
Country Of Origin	MX

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>