

Product data sheet

Specifications



PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

9001K2L38R20

Discontinued on: Dec 19, 2019

Discontinued

Main

| | |
|---------------------------------|----------------------------------|
| Range Of Product | Harmony 9001K |
| Product Or Component Type | Complete illuminated push-button |
| Device Short Name | 9001K |
| Mounting Diameter | 1.18 in (30 mm) |
| Operator Additional Information | Screw-on plastic mushroom |
| Light Source | incandescent |

Complementary

| | |
|------------------------------|--------------------------------|
| Bezel Material | Chromium plated metal |
| Shape Of Signaling Unit Head | Round |
| Type Of Operator | spring return |
| Operator Profile | Red mushroom Ø 35 mm, unmarked |
| Bulb Base | BA 9s |
| Light Block Supply | Direct 120 V AC/DC |
| Mechanical Durability | 5000000 cycles |
| Operating Position | Any position |
| Net Weight | 0.37 lb(US) (0.166 kg) |

Environment

| | |
|---------------------------------------|--|
| Standards | JIS C 852 JIS C 4520 EN/IEC 60947-5-4 EN/IEC 60947-1 CSA C22.2 No 14 UL 508 EN/IEC 60947-5-1 |
| Product Certifications | UL 508 NEMA |
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -40...158 °F (-40...70 °C) |
| Ambient Air Temperature For Operation | -13...158 °F (-25...70 °C) |
| Vibration Resistance | 7 gn 2...500 Hz)IEC 60068-2-6 |
| Shock Resistance | 50 gn IEC 60068-2-27 |
| Electrical Shock Protection Class | Class II IEC 61140 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------|---|
| Ip Degree Of Protection | IP66 IEC 60529 |
| Nema Degree Of Protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 |

Ordering and shipping details

| | |
|-------------------|-----------------------------|
| Category | 21426-9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| Gtin | 00785901180098 |
| Returnability | No |
| Country Of Origin | MX |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|