

Product data sheet

Specifications



PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

9001K2L5G

Discontinued on: Jan 27, 2022

Discontinued

Main

Bezel Material	Chromium plated metal
Control Button Type	standard push-button
Device Short Name	K
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting Diameter	1.18 in (30 mm)
Operator Additional Information	Without guard

Complementary

Cap/Operator Or Lens Colour	green
Contacts Type And Composition	Without contact block
Control Type	illuminated push-button
Light Block Supply	Via transformer 380 V AC 50/60 Hz Via transformer 480 V AC 50/60 Hz
Marking	unmarked
Mounting Support	panel
Operator Position Information	2 positions
Operator Profile	1 projecting push-button
Permissible Voltage	600 V
Shape	Round head
Type Of Operator	Momentary

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Gtin	785901550754
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------