

Product data sheet

Specifications



PUSH BUTTON 600VAC 10A 30MM T-K

9001K2L6GH13

Discontinued on: Oct 11, 2019

Discontinued

Main

Bezel Material	Chromium plated metal
Device Short Name	K
Mounting Diameter	1.18 in (30 mm)

Complementary

Line Rated Current	10 A
Light Block Supply	Via transformer 550 V AC 50/60 Hz Via transformer 6000 V AC 50/60 Hz
Operator Position Information	2 positions
Operator Profile	1 projecting push-button
Utilisation Category	DC-13 AC-15

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications