Product data sheet

Specifications



joystick controller - Ø 30 - 3 vertical positions spring return - w/ o contact

9001K31H7

() Discontinued on: Jan 23, 2021



Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Joystick controller	
Device Short Name	9001K	
Sale Per Indivisible Quantity	1	
Type Of Operator	spring return	
Operator Profile	80 mm long operating shaft	

Complementary

Bezel Material	Chromium plated metal	
Mounting Diameter	1.18 in (30 mm)	
Net Weight	0.82 lb(US) (0.372 kg)	
Operating Position	Vertical	
Shape Of Signaling Unit Head	Octagonal	
Operator Position Information	3 positions	
Contacts Type And Composition	Without contact block	
Device Presentation	Basic element	

Environment

Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Overvoltage Category	II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Standards	UL 508 JIS C8201-5-1 JIS C 852 EN/IEC 60947-5-4 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-1 JIS C8201-1
Product Certifications	NEMA UL 508
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov