# Product data sheet

Specifications





## 30mm Push Button, Type K, joystick controller, 5 positions, spring return, without contacts

9001K35

Product availability: Stock - Normally stocked in distribution facility

### Price\*: 309.00 USD

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for joystick controller
Device Short Name	9001K
Sale Per Indivisible Quantity	1
Type Of Operator	spring return
Operator Profile	80 mm long operating shaft

## Complementary

•	
Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.82 lb(US) (0.372 kg)
Operating Position	Any position
Shape Of Signaling Unit Head	Octagonal
Contacts Type And Composition	Without contact block
Device Presentation	Basic element
Operator Direction Information	4 directions
Type Of Operator	Spring return
Size	30 mm
Return	To centre

## Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Overvoltage Category	II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 4

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Standards	JIS C8201-5-1 JIS C 852 CSA C22.2 No 14 IEC 60947-5-1 UL 508 IEC 60947-1 IEC 60947-5-4 JIS C8201-1
Product Certifications	UL 508 NEMA
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901077145
Returnability	Yes
Country Of Origin	МХ

## **Packing Units**

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	1.65 in (4.200 cm)
Package 1 Length	5.28 in (13.400 cm)
Package 1 Weight	8.50 oz (241.000 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	18
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	10.21 lb(US) (4.633 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information
Yes


## **Certifications & Standards**

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations Circularity Profile			

#### Mounting and Clearance

#### **Contact Block Mounting Position**

Top and Rear views



(1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)

- (2) Operator
- (3) Locating notch


(4) Side 1

(5) Side 2

## Product data sheet

#### Panel Cut-Out


#### Clearance



Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

#### Individual Cut-outs Details

2 alternatives



**Technical Description** 

### **Joystick Positions**

