





# green illuminated push button - Type K - Ø30

9001K3L35GH6

Discontinued on: Jan 23, 2021



#### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Illuminated push-button
Device Short Name	9001K
Type Of Operator	spring return
Operator Profile	Green flush, unmarked
Operator Additional Information	Extended metallic guard

## Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Light Source	incandescent
Bulb Base	BA 9s
Light Block Supply	Direct
[Us] Rated Supply Voltage	2428 V AC/DC
Contacts Type And Composition	1 NC
Connections - Terminals	Screw clamp terminals 1 x 0.222 x 1.5 mm² IEC 60947-1
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1
Mechanical Durability	5000000 cycles
Operating Position	Any position
[le] Rated Operational Current	10 A, AC-15 10 A, DC-13
Contacts Material	Silver alloy contacts
Contact Operation	Standard
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A
[Icm] Rated Short-Circuit Making Capacity	12 kA
Device Presentation	Complete product

### **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	UL listed file E42259 CCN NKCR NEMA CSA LR 25490 class 3211 03 CE
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

## Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

## **Contractual warranty**

Warranty 18 months

Apr 26, 2024



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov