





amber illuminated pushbutton Ø 30 - spring return metallic guard - 120 V AC/DC

9001K3L38A

! Discontinued on: Dec 2, 2020

! End-of-service on: Dec 31, 2020

① Discontinued

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Complete illuminated push-button
Device Short Name	9001K
Mounting Diameter	1.18 in (30 mm)
Operator Additional Information	Extended metallic guard
Light Source	incandescent

Complementary

Bezel Material	Chromium plated metal
Shape Of Signaling Unit Head	Round
Type Of Operator	spring return
Operator Profile	Amber flush, unmarked
Bulb Base	BA 9s
Light Block Supply	Direct 120 V AC/DC
Mechanical Durability	5000000 cycles
Operating Position	Any position
Net Weight	0.37 lb(US) (0.166 kg)

Environment

Standards	EN/IEC 60947-5-4 EN/IEC 60947-5-1 CSA C22.2 No 14 JIS C 852 JIS C 4520 UL 508 EN/IEC 60947-1
Product Certifications	NEMA UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov