## Product data sheet

Specifications



() Discontinued

# selector switch Ø 30 - 3 positions - maintained - incandescent

9001K43J1W

- () Discontinued on: Dec 2, 2020
- (!) End-of-service on: Dec 31, 2020

#### Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Illuminated selector switch	
Device Short Name	9001K	
Type Of Operator	maintained	
Operator Profile	White standard knob	

## Complementary

complementary		
Bezel Material	Chromium plated metal	
Mounting Diameter	1.18 in (30 mm)	
Net Weight	0.54 lb(US) (0.245 kg)	
Shape Of Signaling Unit Head	Round	
Operator Position Information	3 positions	
Contacts Type And Composition	Without contact block	
Mechanical Durability	500000 cycles	
Light Block Supply	Via integral transformer	
Light Source	incandescent	
Bulb Base	BA 9s	
[Us] Rated Supply Voltage	110120 V AC 50/60 Hz	
Device Presentation	Basic element	

## Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 4 NEMA 6

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Standards	EN/IEC 60947-5-1 UL 508 EN/IEC 60947-5-4 CSA C22.2 No 14 JIS C 852
	EN/IEC 60947-1 JIS C 4520
Product Certifications	UL 508 NEMA
Vibration Resistance	7 gn 2…500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

## Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov