Product data sheet

Specifications





illuminated selector switch Ø 30 - green - 3 position - stay put - 24 V AC/DC

9001K46J35LGFG

() Discontinued on: Jan 23, 2021



Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Illuminated selector switch	
Device Short Name	9001K	
Type Of Operator	stay put	
Operator Profile	Amber long handle	

Complementary

oompiementai y	
Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.54 lb(US) (0.245 kg)
Shape Of Signaling Unit Head	Octagonal
Operator Position Information	3 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Light Block Supply	Direct
Light Source	LED
Bulb Base	BA 9s
Light Block Colour	Green
[Us] Rated Supply Voltage	24 V AC/DC
Product Compatibility	9001KA1 side 1 or 2
Device Presentation	Basic element

Environment

Protective Treatment	тс	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Electrical Shock Protection Class	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
Standards	JIS C 4520
	UL 508
	EN/IEC 60947-5-4
	EN/IEC 60947-5-1
	EN/IEC 60947-1
	JIS C 852
	CSA C22.2 No 14
Product Certifications	NEMA
	UL 508
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)	
Discount Schedule	CS1	
Gtin	3389118042933	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.10 in (5.334 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	8.80 oz (249.476 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov