

# Product data sheet

Specifications

SQUARE D



## SELECTOR SWITCH OPERATOR 30MM T-K

9001K52J35WH7

- ⚠ Discontinued on: Dec 2, 2020
- ⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

### Main

Device Short Name	K
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting Diameter	1.18 in (30 mm)

### Complementary

Line Rated Current	10 A
Bezel Material	Chromium plated metal
Cap/Operator Or Lens Colour	white
Contact Operation	Standard fingersafe
Light Block Supply	Full voltage 24 V Full voltage 28 V
Operator Position Information	3 positions
Operator Profile	Standard knob
Operator Profile	1 projecting push-button
Type Of Operator	Spring return both sides to centre
Utilisation Category	DC-13 AC-15

### Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

### Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications