Product data sheet

Specifications



Light block, Harmony 9001K, Harmony 9001SK, 30mm, incandescent bulb, 120V

9001KM38

Product availability: Stock - Normally stocked in distribution facility

Price*: 86.00 USD

Main

Range Of Product	Harmony 9001K Harmony 9001SK	
Product Or Component Type	Light block	
Device Short Name	9001K	
Bulb Base	BA 9s	
Light Block Supply	Direct via integral resistance	

Complementary

· · · · · · · · · · · · · · · · · · ·		
Net Weight	0.11 lb(US) (0.05 kg)	
Light Source	Incandescent bulb	
[Us] Rated Supply Voltage	120 V AC/DC	
[Us] Rated Supply Voltage	120 V	
Light Block Supply	Full voltage or resistor	
Size	30 mm	

Environment

Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ip Degree Of Protection	IP20 IEC 60529	
Standards	IEC 60947-5-1 UL 508 IEC 60947-5-4 IEC 60947-1 CSA C22.2 No 14 JIS C 852 JIS C 4520	
Product Certifications	NEMA UL 508	
Electrical Shock Protection Class	Class II IEC 61140	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US10CS121435	
Discount Schedule	0CS1	
Gtin	785901726623	
Returnability	Yes	
Country Of Origin	МХ	

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	1.80 in (4.572 cm)
Package 1 Weight	2.24 oz (63.503 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product data sheet

Dimensions Drawings

Dimensions



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.