

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 125.00 USD



Main

Range of product	Harmony 9001K
Product or component type	Pilot light
Device short name	K

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Lens type	Fresnel (plastic)
Cap/Operator or lens colour	Blue
Light source	Incandescent
Bulb base	BA 9s
Light block supply	Full voltage Direct
Connections - terminals	Screw clamp terminals (1 x 0.22...2 x 1.5 mm ²) conforming to IEC 60947-1
Shape of screw head	Round head
Operating position	Any position
[Us] rated supply voltage	24...28 V AC/DC
Operating mode	Normal
Device presentation	Complete product

Environment

Product certifications	CSA LR25490 class 3211 03 CE UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901032717
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------