

Product data sheet

Specifications



PUSH BUTTON 600VAC 10A 30MM T-K

9001KR131H6

Discontinued on: Dec 19, 2019

Discontinued

Main

Bezel Material	Chromium plated metal
Control Button Type	key operated push-button
Device Short Name	K
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Light Source	without
Mounting Diameter	1.18 in (30 mm)
Operator Additional Information	Full guard in metal

Complementary

Line Rated Current	10 A
Contact Operation	Standard fingersafe
Contacts Type And Composition	1 NC
Control Type	push-button
Electrical Connection	Screw clamp terminal
Key Number	E10
Light Block Supply	Without supply Without supply
Marking	unmarked
Mounting Support	panel
Operator Position Information	3 positions
Operator Profile	1 projecting push-button
Permissible Voltage	600 V
Shape	Round head
Type Of Operator	Lockable test button extended position locked position
Utilisation Category	AC-15 DC-13

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Gtin	00785901626060
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------