

Product data sheet

Specifications

SQUARE D



PUSHBUTTON OPERATOR 30MM TYPE K +OPTIONS

9001KR141E12

Discontinued on: Dec 19, 2019

Discontinued

Main

Bezel Material	Chromium plated metal
Control Button Type	key operated push-button
Device Short Name	K
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Light Source	without
Mounting Diameter	1.18 in (30 mm)
Operator Additional Information	Full guard in metal

Complementary

Contacts Type And Composition	Without contact block
Control Type	push-button
Key Number	E12
Light Block Supply	Without supply Without supply
Marking	unmarked
Mounting Support	panel
Operator Position Information	3 positions
Operator Profile	1 projecting push-button
Shape	Round head
Type Of Operator	Lockable test button extended position locked or unlocked position
Utilisation Category	AC-15 DC-13

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Gtin	00785901959038

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------