





# PUSH BUTTON 600VAC 10A 30MM T-K

9001KR1WH5Y238

Product availability: Stock - Normally stocked in distribution facility

Price\*: 66.00 USD

### Main

| Range Of Product                | Harmony 9001K         |
|---------------------------------|-----------------------|
| Product Or Component Type       | Push-button           |
| Device Short Name               | 9001K                 |
| Type Of Operator                | spring return         |
| Operator Profile                | flush                 |
| Operator Additional Information | Full quard in plastic |

### Complementary

| Bezel Material                                 | Chromium plated metal                                 |
|--|---|
| Mounting Diameter                              | 1.18 in (30 mm)                                       |
| Shape Of Signaling Unit Head                   | Octagonal   |
| Connections - Terminals                        | Screw clamp terminals 1 x 0.222 x 1.5 mm² IEC 60947-1 |
| Tightening Torque                              | 7.08 lbf.in (0.8 N.m) IEC 60947-1                     |
| Shape Of Screw Head                            | Cross slotted   |
| Mechanical Durability                          | 5000000 cycles  |
| Operating Position                             | Any position  |
| [Uimp] Rated Impulse Withstand Voltage         | 2.5 kV IEC 60947-1                                    |
| Contacts Material                              | Silver alloy contacts                                 |
| Contact Operation                              | Standard  |
| Positive Opening                               | Without   |
| Short-Circuit Protection                       | 10 A cartridge fuse IEC 60947-5-1                     |
| [Ith] Conventional Free Air<br>Thermal Current | 10 A  |
| Device Presentation                            | Complete product                                      |

### **Environment**

| Protective Treatment                  | TC                         |
|---------------------------------------|----------------------------|
| Ambient Air Temperature For Storage   | -40158 °F (-4070 °C)       |
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C)       |
| Vibration Resistance                  | 7 gn 2500 Hz)IEC 60068-2-6 |
| Shock Resistance                      | 50 gn IEC 60068-2-27       |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Electrical Shock Protection Class | Class II IEC 61140 |
|-----------------------------------|--------------------|
| Ip Degree Of Protection           | IP66 IEC 60529     |

# Ordering and shipping details

| Category          | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1         |
| Gtin              | 785901736547 |
| Returnability     | No           |
| Country Of Origin | MX           |

# **Packing Units**

| Unit Type Of Package 1       | PCE                  |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1                    |
| Package 1 Height             | 5.08 in (12.903 cm)  |
| Package 1 Width              | 2.00 in (5.08 cm)    |
| Package 1 Length             | 12.90 in (32.774 cm) |
| Package 1 Weight             | 4.32 oz (122.47 g)   |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | China RoHS declaration  |
| Environmental Disclosure  | Product Environmental Profile   |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |