Product data sheet

Specifications





PUSH BUTTON 600VAC 10A 30MM T-K

9001KR1WH7Y238Y2

() Discontinued on: Mar 8, 2023

() Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Push-button
Device Short Name	9001K
Type Of Operator	spring return
Operator Profile	flush
Operator Additional Information	Full guard in plastic

Complementary

· · · · · · · · · · · · · · · · · ·		
Bezel Material	Chromium plated metal	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Octagonal	
Connections - Terminals	Screw clamp terminals 1 x 0.222 x 1.5 mm ² IEC 60947-1	
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1	
Shape Of Screw Head	Cross slotted	
Mechanical Durability	5000000 cycles	
Operating Position	Any position	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV IEC 60947-1	
Contacts Material	Silver alloy contacts	
Contact Operation	Standard	
Positive Opening	Without	
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A	
Device Presentation	Complete product	

Environment

Protective Treatment	тс	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901956242	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	11.43 in (29.032 cm)	
Package 1 Width	4.50 in (11.43 cm)	
Package 1 Length	29.03 in (73.742 cm)	
Package 1 Weight	8.00 oz (226.796 g)	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov