

Product data sheet

Specifications



PUSH BUTTON 600VAC 10A 30MM T-K

9001KR25RH8

Discontinued on: Oct 11, 2019

Discontinued

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Push-button
Device Short Name	K
Type Of Operator	momentary
Operator Profile	flush
Operator Additional Information	Without guard Screw-on plastic mushroom with set screw

Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Light Source	Without
Light Block Supply	Without supply
Contacts Type And Composition	2 NC
[Ie] Rated Operational Current	10 A, AC-15 10 A, DC-13
Contact Operation	Standard
Device Presentation	Complete product

Environment

Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03 NEMA
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Gtin	00785901626114
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------