





# Push-button head, Harmony 9001K, metal, metal mushroom 60mm, red, 30mm, spring return

9001KR25RM

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 101.00 USD

#### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for push-button
Product Compatibility	Contact block 9001KA
Device Short Name	9001K
Type Of Operator	spring return
Operator Profile	Red mushroom Ø 60 mm, unmarked

#### **Complementary**

Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Cad Overall Width	2.36 in (60 mm)
Cad Overall Height	2.36 in (60 mm)
Cad Overall Depth	2.76 in (70 mm)
Net Weight	0.33 lb(US) (0.15 kg)
Operating Position	Any position
Shape Of Signaling Unit Head	Round
Head Material	Metal
Operator Additional Information	Screw-on metal with set screw
Contacts Type And Composition	Without contact block
Mechanical Durability	5000000 cycles
Device Presentation	Basic element
Cap/Operator Or Lens Colour	Red
Operator Profile	Mushroom Ø 60 mm
Type Of Operator	Spring return
Size	30 mm

#### **Environment**

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 6
Standards	IEC 60947-5-1
	IEC 60947-1
	IEC 60947-5-4
	JIS C 4520
	JIS C 852
	UL 508
	CSA C22.2 No 14
Product Certifications	NEMA
	UL 508
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 an IEC 60068-2-27

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901685869
Returnability	No
Country Of Origin	MX

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.43 in (29.032 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	29.03 in (73.742 cm)
Package 1 Weight	4.80 oz (136.078 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information


Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	No need of specific recycling operations				
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

#### **Dimensions Drawings**

#### **Dimensions**






 $\boldsymbol{e}$  panel thickness: 1 to 6 mm / 0.04 to 0.24 in.  $\boldsymbol{a}$  28 mm / 1.10 in.

#### 9001KR25RM

#### Mounting and Clearance

#### **Contact Block Mounting Position**


Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

#### Panel Cut-Out

#### Clearance



Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	57.2	2.25
9001KN3••	57.2	2.25	57.2	2.25

#### **Individual Cut-outs Details**

2 alternatives

