



Price\*\* : 118.00 USD

9001KR8RH5 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

### Main

Bezel material	Chromium plated metal
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor
Light source	Without
Mounting diameter	1.18 in (30 mm)
Operator additional information	Without guard Screw-on plastic mushroom 1.63 in

### Complementary

Line Rated Current	10 A
Cap/Operator or lens colour	Red
Contact operation	Standard fingersafe
Contacts type and composition	1 NO
Control type	Push-button
Electrical connection	Screw clamp terminal
Light block supply	Without supply
Marking	Unmarked
Mounting support	Panel
Operator position information	3 positions
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Momentary Maintained
Utilisation category	DC-13 AC-15

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
---------------------------	-------------------------

---

Product certifications	CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR
------------------------	---

---

**Ordering and shipping details**

---

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---