# **Product data sheet**

Specifications





30mm Push Button, Type K, illuminated push pull operator, transformer, 120 VAC, red mushroom cap, 1 NO and 1 NC

9001KR9P1RH13

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 316.00 USD

#### Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Illuminated push-button	
Device Short Name	к	
Type Of Operator	push-pull	
Operator Profile	Red mushroom Ø 41 mm	
Operator Additional Information	Screw-on plastic	

#### Complementary

Complementary		
Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Light Source	incandescent	
Light Source	Incandescent bulb	
Bulb Base	BA 9s	
Light Block Supply	Via integral transformer	
[Us] Rated Supply Voltage	110120 V AC	
Contacts Type And Composition	1 C/O	
Connections - Terminals	Screw clamp terminals	
Operating Position	Any position	
[le] Rated Operational Current	10 A, AC-15 10 A, DC-13	
Contact Operation	Standard	
Device Presentation	Complete product	
Cap/Operator Or Lens Colour	Red	
[Us] Rated Supply Voltage	110120 V	
Light Block Supply	Via integral transformer	
Operator Profile	Mushroom Ø 41 mm	
Type Of Operator	Push-pull	
Operator Position Information	2 positions	
Supply Frequency	5060 Hz	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Size

### Environment

Product Certifications	UL listed file E42259 CCN NKCR CE NEMA CSA LR 25490 class 3211 03
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

# Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901821083	
Returnability	Yes	
Country Of Origin	МХ	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	9.76 oz (276.691 g)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance



Rohs Exemption Information

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov