





Selector switch head, Harmony 9001K, metal, long handle, black, 30mm, 2 positions, spring return left to right

9001KS25FB





Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Head for selector switch	
Device Short Name	9001KS	
Type Of Operator	Left to right spring return	
Operator Profile	Black gloved hand knob	

Complementary

Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Net Weight	0.54 lb(US) (0.245 kg)	
Shape Of Signaling Unit Head	Round	
Operator Position Information	2 positions	
Contacts Type And Composition	Without contact block	
Mechanical Durability	500000 cycles	
Device Presentation	Basic element	
Cap/Operator Or Lens Colour	Black	
Operator Profile	Long handle	
Type Of Operator	Spring return	
Size	30 mm	
Return	Left to right	
Cam Profile	5	

Environment

Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Overvoltage Category	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4	
	NEMA 6	
Standards	JIS C 4520 UL 508 EN/IEC 60947-1 JIS C 852 CSA C22.2 No 14 EN/IEC 60947-5-4 EN/IEC 60947-5-1	
Product Certifications	NEMA UL 508	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	

Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901346968	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	7.62 in (19.355 cm)	
Package 1 Width	3.00 in (7.62 cm)	
Package 1 Length	19.35 in (49.161 cm)	
Package 1 Weight	8.00 oz (226.796 g)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov