

Product data sheet

Specifications

SQUARE D



SELECTOR SWITCH OPERATOR 30MM T-K

9001KS53K5B602

Discontinued on: Oct 11, 2019

Discontinued

Main

Range Of Product	Harmony 9001KS
Product Or Component Type	Selector switch
Device Short Name	9001K
Type Of Operator	To centre spring return
Operator Profile	key switch

Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.52 lb(US) (0.234 kg)
Shape Of Signaling Unit Head	Octagonal
Operator Position Information	3 positions
Type Of Keylock	E10
Key Number	E10
Key Withdrawal Position	Center
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Product Compatibility	9001KA1 side 1 or 2
Device Presentation	Basic element

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60947-5-4 JIS C 852 EN/IEC 60947-5-1 UL 508 EN/IEC 60947-1 JIS C 4520 CSA C22.2 No 14
Product Certifications	NEMA UL 508
Vibration Resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Gtin	00785901838081
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------