

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 231.00 USD



### Main

Bezel material	Chromium plated metal
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor
Mounting diameter	1.18 in (30 mm)

### Complementary

Line Rated Current	10 A
Cap/Operator or lens colour	Black
Contact operation	Standard fingersafe
Contacts type and composition	1 NO + 1 NC
Control type	Push-button
Electrical connection	Screw clamp terminal
Key number	E10
Key withdrawal position	Center
Mounting support	Panel
Operator position information	3 positions
Operator profile	Key operated knob
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Spring return left to centre
Utilisation category	DC-13 AC-15

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE

### Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901851035
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

### Contractual warranty

Warranty period	18 months
-----------------	-----------