Product data sheet

Specification





Push to test pilot light head, Harmony 9001K, metal, without cap, 30mm, 110...120V

9001KT1

Product availability: Stock - Normally stocked in distribution facility

Price*: 185.00 USD

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Head for push-to-test pilot light	
Device Short Name	К	

Complementary

Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Cap/Operator Or Lens Colour	Without cap	
Bulb Base	BA 9s	
Light Block Supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz	
Shape Of Screw Head	Round	
Light Source	Incandescent bulb	
Operating Mode	Push-to-test	
[Us] Rated Supply Voltage	110120 V	
Light Block Supply	Via integral transformer	
Contacts Type And Composition	1 C/O	
Supply Frequency	5060 Hz	
Size	30 mm	

Environment

Product Certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901170297	
Returnability	Yes	
Country Of Origin	US	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.080 cm)
Package 1 Width	2.30 in (5.842 cm)
Package 1 Length	4.50 in (11.430 cm)
Package 1 Weight	9.12 oz (258.500 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	14
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.42 lb(US) (3.819 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	448
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	287.06 lb(US) (130.208 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations Circularity Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov