

Product data sheet

Characteristics

9001KT7G6

PILOT LIGHT 120VAC 30MM TYPE K +OPTIONS

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 197.00 USD



Main

Bezel material	Chromium plated metal
Device short name	K
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor
Lens type	Domed glass
Mounting diameter	1.18 in (30 mm)

Complementary

Cap/Operator or lens colour	Green
Electrical connection	Screw clamp terminal
Light block supply	Via transformer 220 V AC 50/60 Hz Via transformer 240 V AC 50/60 Hz
Operating mode	Push-to-test
Shape	Round head

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901909958
Nbr. of units in pkg.	1
Package weight(Lbs)	0.4000000000000002

Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------