



Price* : 4.40 USD

9001KXN762 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range of product	Harmony 9001K
Product or component type	Selector switch
Device short name	9001K
Type of operator	Spring return (outside left/right to inside left/right)
Operator profile	Yellow standard knob

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Product weight	0.54 lb(US) (0.245 kg)
Shape of signaling unit head	Round
Operator position information	3 positions
Contacts type and composition	Without contact block
Mechanical durability	500000 cycles
Device presentation	Basic element

Environment

Protective treatment	TC
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529
Vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27

Ordering and shipping details

Category	21427 - 9001 KX
Discount Schedule	CS1

GTIN	00785901524212
Nbr. of units in pkg.	50
Package weight(Lbs)	0.01
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------