





Illuminated push-button head, Harmony 9001SK, plastic, plastic guard flush, blue, 30mm, spring return, 24-28V

9001SK1L35L

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 138.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for illuminated push-button
Device Short Name	9001SK

Complementary

Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Octagonal	
Type Of Operator	spring return	
Operator Profile	Blue flush, unmarked	
Operator Additional Information	Plastic guard	
Light Source	incandescent	
Bulb Base	BA 9s	
Light Block Supply	Direct 2428 V AC/DC	
Contacts Type And Composition	Without contact block	
Standards	UL 508 JIS C 4520 EN/IEC 60947-1 EN/IEC 60947-5-4 JIS C 852 EN/IEC 60947-5-1 CSA C22.2 No 14	
Product Certifications	UL 508 NEMA CSA LR25490 class 3211 03 UL listed file E78403 CCN NKCR	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	
Electrical Shock Protection Class	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1	
	NEMA 12	
	NEMA 13	
	NEMA 2	
	NEMA 3	
	NEMA 3R	
	NEMA 4	
	NEMA 4X	
Mechanical Durability	5000000 cycles	
Operating Position	Any position	
Net Weight	0.40 lb(US) (0.181 kg)	
Cap/Operator Or Lens Colour	Blue	
[Us] Rated Supply Voltage	2428 V	
Light Block Supply	Full voltage	
Operator Profile	Flush	
Type Of Operator	Spring return	
Size	30 mm	
Light Source	Incandescent bulb	

Ordering and shipping details

Category	US10CS121429	
Discount Schedule	0CS1	
Gtin	785901158639	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.08 in (12.903 cm)	
Package 1 Width	2.00 in (5.08 cm)	
Package 1 Length	12.90 in (32.774 cm)	
Package 1 Weight	6.40 oz (181.437 g)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov