

Product data sheet

Specifications



amber illum pushbutton Ø 30 -
flush spring return full guard - 120
V AC/DC

9001SK1L38A

Discontinued on: Oct 11, 2019

Discontinued

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-button
Device Short Name	9001SK

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Octagonal
Type Of Operator	spring return
Operator Profile	Amber flush, unmarked
Operator Additional Information	Full guard in plastic
Light Source	incandescent
Bulb Base	BA 9s
Light Block Supply	Direct 120 V AC/DC
Standards	JIS C 852 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-1 UL 508 EN/IEC 60947-5-1 JIS C 4520
Product Certifications	NEMA UL 508 CSA LR25490 class 3211 03 UL listed file E78403 CCN NKCR
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Vibration Resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 4X
Mechanical Durability	5000000 cycles
Operating Position	Any position
Net Weight	0.40 lb(US) (0.181 kg)

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Gtin	00785901116707
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------