

# 9001SK1L38AH6

## PUSHBUTTON 600VAC 10AMP 30MM SK +OPTIONS



Price\* : 177.00 USD

9001SK1L38AH6 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

### Main

Bezel material	Black plastic
Control button type	Standard push-button
Device short name	SK
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Mounting diameter	1.18 in (30 mm)
Operator additional information	Full guard in plastic

### Complementary

Line Rated Current	10 A
Cap/Operator or lens colour	Amber
Contact operation	Standard fingersafe
Contacts type and composition	1 NC
Control type	Illuminated push-button
Electrical connection	Screw clamp terminal
Light block supply	Direct 120 V Full voltage
Marking	Unmarked
Mounting support	Panel
Operator position information	2 positions
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Momentary
Utilisation category	DC-13 AC-15

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

## Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.40000000000000002
Returnability	N
Country of origin	MX

## Contractual warranty

Warranty period	18 months
-----------------	-----------