

9001SK1L38WH13

PUSHBUTTON 600VAC 10AMP 30MM SK +OPTIONS



Price* : 198.00 USD

9001SK1L38WH13 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

| | |
|---------------------------------|---|
| Bezel material | Black plastic |
| Control button type | Standard push-button |
| Device short name | K |
| Enclosure type | Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor |
| Mounting diameter | 1.18 in (30 mm) |
| Operator additional information | Full guard in plastic |

Complementary

| | |
|-------------------------------|------------------------------|
| Line Rated Current | 10 A |
| Cap/Operator or lens colour | White |
| Contact operation | Standard fingersafe |
| Contacts type and composition | 1 NO + 1 NC |
| Control type | Illuminated push-button |
| Electrical connection | Screw clamp terminal |
| Light block supply | Full voltage Direct 120 V |
| Marking | Unmarked |
| Mounting support | Panel |
| Operator position information | 2 positions |
| Operator profile | 1 projecting push-button |
| Permissible voltage | <= 600 V |
| Shape | Round head |
| Type of operator | Momentary |
| Utilisation category | AC-15 DC-13 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|---------------------------|---|
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13 |
| Product certifications | CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 |

Ordering and shipping details

| | |
|-----------------------|---------------------|
| Category | 21429 - 9001 SK,SKY |
| Discount Schedule | CS1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.40000000000000002 |
| Returnability | N |
| Country of origin | MX |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|