

9001SK1L7CH5

PUSHBUTTON 600VAC 10AMP 30MM SK +OPTIONS



Price* : 208.00 USD

9001SK1L7CH5 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Bezel material	Black plastic
Control button type	Standard push-button
Device short name	SK
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Mounting diameter	1.18 in (30 mm)
Operator additional information	Full guard in plastic

Complementary

Line Rated Current	10 A
Cap/Operator or lens colour	Clear
Contact operation	Standard fingersafe
Contacts type and composition	1 NO
Control type	Illuminated push-button
Electrical connection	Screw clamp terminal
Light block supply	Via transformer 220 V AC 50/60 Hz Via transformer 240 V AC 50/60 Hz
Marking	Unmarked
Mounting support	Panel
Operator position information	2 positions
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Momentary
Utilisation category	AC-15 DC-13

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.40000000000000002
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------