





# green illum pushbutton Ø 30 - flush spring return full guard - 220/240 V AC

9001SK1L7G

! Discontinued on: Dec 2, 2020

! End-of-service on: Dec 31, 2020

## ① Discontinued

#### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-button
Device Short Name	9001SK

### Complementary

Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Octagonal	
Type Of Operator	spring return	
Operator Profile	Green flush, unmarked	
Operator Additional Information	Full guard in plastic	
Light Source	incandescent	
Bulb Base	BA 9s	
Light Block Supply	Direct 220240 V AC 50/60 Hz	
Standards	CSA C22.2 No 14 UL 508 EN/IEC 60947-1 JIS C 852 EN/IEC 60947-5-4 EN/IEC 60947-5-1 JIS C 4520	
Product Certifications	CSA LR25490 class 3211 03 UL listed file E78403 CCN NKCR UL 508 NEMA	
Protective Treatment	TC	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	
Electrical Shock Protection Class	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 4X
Mechanical Durability	5000000 cycles
Operating Position	Any position
Net Weight	0.40 lb(US) (0.181 kg)

## Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Gtin	00785901838098
Returnability	No
Country Of Origin	MX

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov